

### SonaSpray K-13 Standard Finish

#### SONASPRAY K-13 STANDARD ON SOLID BACKING

THICKNESS	125 Hz	250 Hz	500 Hz	1,000 Hz	2,000 Hz	4,000 Hz	$\alpha_w$ [-]	NRC
10 mm	0,10	0,20	0,46	0,66	0,78	0,89	<b>0,45</b>	<b>0,55</b>
15 mm	0,17	0,26	0,63	0,85	0,93	0,98	<b>0,55</b>	<b>0,65</b>
20 mm	0,16	0,34	0,74	0,95	0,97	0,94	<b>0,60</b>	<b>0,74</b>
25 mm	0,23	0,49	0,87	0,96	0,97	0,86	<b>0,75</b>	<b>0,80</b>
35 mm	0,26	0,62	1,02	1,07	1,01	0,96	<b>0,90</b>	<b>0,95</b>
45 mm	0,33	0,77	1,12	1,11	1,01	0,93	<b>1,00</b>	<b>1,00</b>



### SonaSpray K-13 Special Finish

#### SONASPRAY K-13 SPECIAL ON SOLID BACKING

THICKNESS	125 Hz	250 Hz	500 Hz	1,000 Hz	2,000 Hz	4,000 Hz	$\alpha_w$ [-]	NRC
10 mm	0,15	0,28	0,59	0,86	0,95	1,02	<b>0,55</b>	<b>0,65</b>
15 mm	0,15	0,33	0,69	0,95	0,98	0,97	<b>0,60</b>	<b>0,75</b>
20 mm	0,16	0,33	0,75	0,96	0,98	0,97	<b>0,60</b>	<b>0,75</b>
25 mm	0,20	0,44	0,89	1,01	0,98	0,93	<b>0,70</b>	<b>0,85</b>



### SonaSpray FC Finish

#### SONASPRAY FC ON SOLID BACKING

THICKNESS	125 Hz	250 Hz	500 Hz	1,000 Hz	2,000 Hz	4,000 Hz	$\alpha_w$ [-]	NRC
10 mm	0,10	0,20	0,48	0,77	0,90	1,00	<b>0,45</b>	<b>0,60</b>
15 mm	0,12	0,25	0,62	0,92	0,98	1,02	<b>0,50</b>	<b>0,70</b>
20 mm	0,17	0,37	0,82	1,04	1,00	0,97	<b>0,65</b>	<b>0,80</b>
25 mm	0,18	0,42	0,88	1,05	0,99	0,97	<b>0,70</b>	<b>0,85</b>

